



R27059010



**R 2705 White 9010 Flat corner**

**Technical properties**

**Architecture**

Fixing mode Hold in position thanks to lid

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility LFS

**Dimensions**

Trunking height 60 mm

Trunking width 150 mm

Measure a 50 mm

**Cover, door**

Lid with softlip -

**Materials**

Colour pure white

RAL colour RAL 9010 - Pure white

Material Steel

Type of surface treatment Painted

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Moulded

**Safety**

Protection index IP IP30

Impact strength IK08

**Use conditions**

Operating temperature -5...90 °C