



R2705VERZ



## R 2705 Galv Flat Corner

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Product compatibility	LFS
-----------------------	-----

#### Dimensions

Trunking height	60 mm
Trunking width	150 mm
Measure a	50 mm

#### Cover, door

Lid with softlip	-
------------------	---

#### Materials

Colour	zinc coated
Material	Steel
Type of surface treatment	Galvanised

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Settings

Angle range	90 °
-------------	------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Safety

Protection index IP	IP30
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Operating temperature	-5...90 °C
-----------------------	------------