



R27319010



Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 60 mm

Length 50 mm

Trunking width 200 mm

Measure a 50 mm

Cover, door

Lid with softlip -

Materials

RAL colour RAL 9010 - Pure white

Material Steel

Material group steel

Type of surface treatment Painted

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHs voluntary compliance

Safety

Protection index IP IP30

Use conditions

Operating temperature -5...90 °C