



R27539010



### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Product compatibility	LF
-----------------------	----

#### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

#### Dimensions

Trunking height	60 mm
-----------------	-------

Trunking width	200 mm
----------------	--------

#### Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	Steel
----------	-------

Material group	steel
----------------	-------

Type of surface treatment	Painted
---------------------------	---------

#### Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

#### Safety

Protection index IP	IP30
---------------------	------

#### Use conditions

Operating temperature	-5...90 °C
-----------------------	------------