



RLA144X

**pet-tolerant anti-masking external movement detector**

**Technical properties**

**Connectivity**

Connection mode radio TwinBand

**Voltage**

Operating voltage 3600 mV

**Electric current**

Current consumption (operation) 28 mA

**Dimensions**

Dimensions (LLxwxhh) 71X106X186

**Measurement**

Detection Method Passive Infrared

**Detection**

Range of detection 12 m

**Equipment**

Angle of horizontal detection 90 °

**Use**

Lense type Pet-tolerant

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP55

**Use conditions**

Operating temperature -20...60 °C