



RLA176X

Pet-tolerant IR detector-camera with sending pictures

Technical properties

Connectivity

Connection mode radio TwinBand

Voltage

Operating voltage 4500 mV

Dimensions

Dimensions (LLxwxhh) 67x85x128 mm

Measurement

Detection Method Passive Infrared

Camera

Shot recording Colour images that are saved locally on the internal memory card

Detection

Range of detection 12 m

Equipment

Angle of horizontal detection 90 °

Use

Lense type Pet-tolerant

Standards

European directive WEEE concerned

Use conditions

Operating temperature 0...55 °C