



S155-22X

**Smoke detector, radio, 10 year-lithium battery**

**Technical properties**

**Architecture**

Fixing mode	Screwed
-------------	---------

**Functions**

Operating type	System
Built-in sounder	Yes, 85 dB at 3 m
Smoke switcher	No

**Connectivity**

Standard network connexion by cable	No
Optional interconnection by radio	No
Standard interconnection by radio	Yes
Networkable	Yes

**Voltage**

Input voltage	≈ 6 V
---------------	-------

**Dimensions**

Dimensions (LLxwwxhh)	116x49 mm
-----------------------	-----------

**Network voltage**

With voltage indication	No
-------------------------	----

**Measurement**

Detection Range	50 m <sup>2</sup>
Detection Method	Optical

**Battery**

life of battery	10 years lithium battery no replacaeble
Weak battery warning	Yes

**Scope of delivery**

Rechargeable battery backup included	No
Type of battery backup included	none

**Equipment**

Number of connexions for sensors / actuator	40
Standalone	No
VDS accepted	No
Sounder volume	85 dB

---

**Standards**

---

Q-Label certification	No
European directive WEEE	concerned

---

**Safety**

---

Protection index IP	IP22
---------------------	------

---

**Use conditions**

---

Operating temperature	-10...65 °C
-----------------------	-------------

---