



S165-22X

**Expert pet tolerant motion detector, 85°, 12 meters**

**Technical properties**

**Connectivity**

Connection mode radio TwinBand

**Voltage**

Operating voltage 3 V

**Dimensions**

Dimensions (LLxwwxhh) 58 x 102 x 57 mm

**Measurement**

Detection Method Passive Infrared

**Detection**

Range of detection 12 m

**Equipment**

Angle of horizontal detection 85 °

**Use**

Lense type Pet-tolerant

**Standards**

European directive WEEE concerned

**Use conditions**

Operating temperature -10...40 °C

**temperatur**

Ambient temperature 10...40 °C