



SA280



Trip free switch 2P 80A

Technical properties

Architecture

Number of poles	2 P
Type of pole	2 P

Configuration

Number of modules	2.5
-------------------	-----

Main electrical features

Rated operational voltage U _e	230 V
--	-------

Voltage

Type of voltage input 1	AC
-------------------------	----

Electric current

Rated current	80 A
Rated short-time withstand current 1s	960 A

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	44 mm

Power

Total power loss under I _N	12.33 W
Power loss per pole at I _N	6.07 W

Connection

Type of connection	with screw
--------------------	------------

Equipment

Quantity of NC contacts	1
Quantity of NO contacts	3
Quantity of INV contacts	0

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
Halogen free	No

Use conditions

Operating temperature	-25...40 °C
Storage/transport temperature	-25...70 °C