



SA280



## Trip free switch 2P 80A

### Technical properties

#### Architecture

Type of order	Break switch
Number of poles	2 P
Type of pole	2 P

#### Configuration

Number of modules	2.5
-------------------	-----

#### Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

#### Voltage

Type of voltage input 1	AC
-------------------------	----

#### Electric current

Rated current	80 A
Rated short-time withstand current 1s	960 A

#### Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	44 mm

#### Power

Total power loss under IN	12.33 W
Power loss per pole at In	6.07 W

#### Installation, mounting

Tightening torque	2,7Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	SW: 6 to 25mm <sup>2</sup> / Aux:0,5 to 6mm <sup>2</sup>
Connection cross-sect. rigid cable	Sw: 6 / 25mm <sup>2</sup> - Aux: 1 / 10mm <sup>2</sup>
Type of connection	with screw

#### Equipment

Quantity of NC contacts	1
Quantity of NO contacts	3
Quantity of INV contacts	0

#### Safety

Halogen free

No

**Use conditions**

Operating temperature

-25...40 °C

Storage/transport temperature

-25...70 °C