



SA440



Trip free switch 4P 40A

Technical properties

Architecture

Number of poles	4 P
Type of pole	4 P

Configuration

Number of modules	4.5
-------------------	-----

Main electrical features

Rated operational voltage Ue	230 / 415 V
------------------------------	-------------

Voltage

Type of voltage input 1	AC
-------------------------	----

Electric current

Rated current	40 A
Rated short-time withstand current 1s	800 A

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	79 mm

Power

Total power loss under I _N	8.01 W
Power loss per pole at I _N	1.56 W

Connection

Type of connection	with screw
--------------------	------------

Equipment

Quantity of NC contacts	1
Quantity of NO contacts	5
Quantity of INV contacts	0

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
Halogen free	No

Use conditions

Operating temperature	-25...40 °C
Storage/transport temperature	-25...70 °C