



SBN133

1-pole, 32A Modular Switch with big terminals

Technical properties

Architecture

Type of order	Break switch
Neutral position	without neutral
Number of poles	1 P
Type of pole	1 P

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Voltage

Type of voltage input 1	AC
-------------------------	----

Electric current

Rated current	32 A
Thermal rated current outside of housings	32 A

Dimensions

Depth of installed product	68 mm
----------------------------	-------

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	1.2 W
Power loss per pole at In	1.2 W

Connection

Type of connection	with screw
--------------------	------------

Equipment

Quantity of NC contacts	0
Quantity of NO contacts	1
Quantity of INV contacts	0

Standards

Standard text	IEC 60947-3 ; IEC/EN 60669-2 ; IEC/EN 60669-4
---------------	---