

68 mm



## SBN333

## 3-pole, 32A Modular Switch with big terminals

## **Technical properties**

Depth of installed product

Architecture	
Type of order	Break switch
Neutral position	without neutral
Number of poles	3 P
Type of pole	3 P
Configuration	
Number of modules	2

Main electrical features	
Rated operational voltage Ue	400 V
Frequency	50/60 Hz
Voltage	
Type of voltage input 1	AC

Electric current		
Rated current	32 A	

Thermal rated current outside of housings	32 A
Dimensions	

Frequency	
Frequency	50 to 60 Hz

Power		
Total power loss under IN	3.5 W	
Power loss per pole at In	1.2 W	

Total power loss under IN	3.5 W
Power loss per pole at In	1.2 W

Type of connection	with screw
Equipment	
Quantity of NC contacts	0
Quantity of NO contacts	3

Canada Ca	_
Quantity of NO contacts	3
Quantity of INV contacts	0

Standards		
Standard text	IEC 60947-3 ; IEC/EN 60669-2 ; IEC/EN 60669-4	

Connection

REACH conform	Yes
RoHS conform	Yes
Halogen free	No