



SBN333

**3-pole, 32A Modular Switch with big terminals**

**Technical properties**

**Architecture**

Type of order	Break switch
Neutral position	without neutral
Number of poles	3 P
Type of pole	3 P

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Rated operational voltage Ue	400 V
Frequency	50/60 Hz

**Voltage**

Type of voltage input 1	AC
-------------------------	----

**Electric current**

Rated current	32 A
Thermal rated current outside of housings	32 A

**Dimensions**

Depth of installed product	68 mm
----------------------------	-------

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under IN	3.5 W
Power loss per pole at In	1.2 W

**Connection**

Type of connection	with screw
--------------------	------------

**Equipment**

Quantity of NC contacts	0
Quantity of NO contacts	3
Quantity of INV contacts	0

**Standards**

Standard text	IEC 60947-3 ; IEC/EN 60669-2 ; IEC/EN 60669-4
European directive WEEE	concerned

