


SK600



## Selector switch non spring ret

### Technical properties

#### Architecture

Number of poles 1 P

#### Configuration

Number of modules 3

#### Controls and indicators

Number of positions of the switch 3

#### Main electrical features

Rated operational voltage  $U_e$  660 V

Frequency 50 Hz

#### Voltage

Rated insulation voltage 690 V

#### Electric current

Rated current 20 A

#### Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 53 mm

#### Power

Total power loss under IN 0.7 W

#### Connection

Number of contacts 1

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -10...40 °C

Storage/transport temperature -40...80 °C