




SK600



Selector switch non spring ret

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 1 P |
|-----------------|-----|

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Controls and indicators

| | |
|-----------------------------------|---|
| Number of positions of the switch | 3 |
|-----------------------------------|---|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 660 V |
|------------------------------|-------|

| | |
|-----------|-------|
| Frequency | 50 Hz |
|-----------|-------|

Voltage

| | |
|--------------------------|-------|
| Rated insulation voltage | 690 V |
|--------------------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

Dimensions

| | |
|----------------------------|-------|
| Depth of installed product | 64 mm |
|----------------------------|-------|

| | |
|-----------------------------|-------|
| Height of installed product | 85 mm |
|-----------------------------|-------|

| | |
|----------------------------|-------|
| Width of installed product | 53 mm |
|----------------------------|-------|

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 0.7 W |
|---------------------------|-------|

Connection

| | |
|---|-------------------------|
| Connection cross-sect. flexible conductor | 1,5 / 10mm ² |
|---|-------------------------|

| | |
|------------------------------------|----------------------|
| Connection cross-sect. rigid cable | 1 / 6mm ² |
|------------------------------------|----------------------|

| | |
|--------------------|---|
| Number of contacts | 1 |
|--------------------|---|

| | |
|------------------|-------|
| Type of contacts | NO-NC |
|------------------|-------|

| | |
|--------------------|------------|
| Type of connection | with screw |
|--------------------|------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...40 °C |
|-----------------------|-------------|

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -40...80 °C |
|-------------------------------|-------------|