




SK601



Reverser 20 2F

Technical properties

Architecture

Number of poles	2 P
-----------------	-----

Configuration

Number of modules	3
-------------------	---

Controls and indicators

Number of positions of the switch	3
-----------------------------------	---

Main electrical features

Rated operational voltage Ue	660 V
------------------------------	-------

Frequency	50 Hz
-----------	-------

Voltage

Rated insulation voltage	690 V
--------------------------	-------

Electric current

Rated current	20 A
---------------	------

Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	53 mm
----------------------------	-------

Connection

Connection cross-sect. flexible conductor	1,5 / 10mm ²
---	-------------------------

Connection cross-sect. rigid cable	1 / 6mm ²
------------------------------------	----------------------

Number of contacts	2
--------------------	---

Type of contacts	NO-NC
------------------	-------

Type of connection	with screw
--------------------	------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------