

-40...80 °C



SK601

Reverser 20 2F

Technical properties

Architecture	
Number of poles	2 P
Configuration	
Number of modules	3
Controls and indicators	
Number of positions of the switch	3
Main electrical features	
Rated operational voltage Ue	660 V
Frequency	50 Hz
Voltage	
Rated insulation voltage	690 V
Electric current	
Rated current	20 A
Dimensions	
Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	53 mm
Connection	
Connection cross-sect. flexible conductor	1,5 / 10mm²
Connection cross-sect. rigid cable	1 / 6mm²
Number of contacts	2
Type of contacts	NO-NC
Type of connection	with screw
Safety	
REACH conform	Yes
RoHS conform	Yes
Use conditions	
Operating temperature	-1040 °C

Storage/transport temperature