



SK602



Voltmeter switch 3"o

Technical properties

Configuration

Number of modules	3
-------------------	---

Controls and indicators

Number of positions of the switch	7
-----------------------------------	---

Main electrical features

Rated operational voltage Ue	660 V
Frequency	50 Hz

Voltage

Rated insulation voltage	690 V
--------------------------	-------

Electric current

Rated current	20 A
---------------	------

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Total power loss under IN	1 W
---------------------------	-----

Network configuration

Network type	tree-phase with neutral
--------------	-------------------------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. rigid cable	1 / 6mm ²
Type of connection	with screw

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...40 °C
Storage/transport temperature	-40...80 °C