




SK603



## Ammeter switch 3 O

### Technical properties

#### Configuration

Number of modules	3
-------------------	---

#### Controls and indicators

Number of positions of the switch	4
-----------------------------------	---

#### Main electrical features

Rated operational voltage Ue	660 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	690 V
--------------------------	-------

#### Electric current

Rated current	20 A
---------------	------

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	70 mm

#### Power

Total power loss under IN	1 W
---------------------------	-----

#### Network configuration

Network type	tree-phase with neutral
--------------	-------------------------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	1,5 / 10mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 6mm <sup>2</sup>
Type of connection	with screw

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...40 °C
Storage/transport temperature	-40...80 °C