



SK604



Changeover switch 4DIRo

Technical properties

Configuration

Number of modules	3
-------------------	---

Controls and indicators

Number of positions of the switch	5
-----------------------------------	---

Main electrical features

Frequency	50 Hz
-----------	-------

Voltage

Rated insulation voltage	690 V
--------------------------	-------

Electric current

Rated current	20 A
---------------	------

Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

Power

Total power loss under IN	1 W
---------------------------	-----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------