




SK606



## Switch with key 10A

### Technical properties

#### Architecture

Number of poles 2 P

#### Configuration

Number of modules 3

#### Controls and indicators

Indicator lamp no

Number of positions of the switch 2

#### Main electrical features

Rated operational voltage  $U_e$  400 V

Frequency 50 Hz

#### Voltage

Rated insulation voltage 440 V

#### Electric current

Rated current 10 A

#### Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 70 mm

#### Power

Total power loss under IN 1 W

#### Connection

Connection cross-sect. flexible conductor 1,5 / 10mm<sup>2</sup>

Connection cross-sect. rigid cable 1 / 6mm<sup>2</sup>

Number of contacts 2

Type of contacts 1NO

Type of connection with screw

#### Safety

REACH conform Yes

RoHS conform Yes

#### Use conditions

Operating temperature -10...40 °C

