




SK606



Switch with key 10A

Technical properties

Architecture

Number of poles 2 P

Configuration

Number of modules 3

Controls and indicators

Indicator lamp no

Number of positions of the switch 2

Main electrical features

Rated operational voltage U_e 400 V

Frequency 50 Hz

Voltage

Rated insulation voltage 440 V

Electric current

Rated current 10 A

Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 70 mm

Power

Total power loss under IN 1 W

Connection

Connection cross-sect. flexible conductor 1,5 / 10mm²

Connection cross-sect. rigid cable 1 / 6mm²

Number of contacts 2

Type of contacts 1NO

Type of connection with screw

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...40 °C

