




SK606



Switch with key 10A

Technical properties

Architecture

Number of poles	2 P
-----------------	-----

Configuration

Number of modules	3
-------------------	---

Controls and indicators

Indicator lamp	no
Number of positions of the switch	2

Main electrical features

Rated operational voltage U _e	400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	440 V
--------------------------	-------

Electric current

Rated current	10 A
---------------	------

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Total power loss under IN	1 W
---------------------------	-----

Connection

Number of contacts	2
Type of contacts	1NO

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...40 °C
Storage/transport temperature	-40...80 °C