



Trunking 11x40, grey

Technical properties

Configuration

Antibacterial treatment	No
Self-adhesive	No

Dimensions

Trunking height	11 mm
Length	2000 mm
Trunking width	40 mm
Width of installed product	40 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	1
Maximum number of cables (Ø 11 mm, 50% fill)	1

Cover, door

Lid with softlip	No
------------------	----

Materials

Colour	stone grey
Material group	plastic
Type of surface treatment	untreated

Equipment

Compartment quantity	1
Number of channels	1

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Impact strength	IK07
-----------------	------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------

SL1104007030

