



SL1104007030



Trunking 11x40, grey

Technical properties

Configuration

Antibacterial treatment	No
Self-adhesive	No

Dimensions

Trunking height	11 mm
Length	2000 mm
Trunking width	40 mm
Width of installed product	40 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	1
Maximum number of cables (Ø 11 mm, 50% fill)	1

Cover, door

Lid with softlip	No
------------------	----

Materials

Material group	plastic
Type of surface treatment	untreated

Equipment

Compartment quantity	1
Number of channels	1

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

temperatur

Ambient temperature	-5...65 °C
---------------------	------------