



SL200551



Trunking base SL200551 black

Technical properties

Dimensions

Trunking height	55 mm
Length	2000 mm
Trunking width	20 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	4
Cable capacity 11mm D e.g. NYM 3 x 1.5mm ² 1st chamber	2 Part
Cable capacity 11mm D e.g. NYM 3 x 1.5mm ² 2nd chamber	3 Part

Materials

Colour	black
Material group	plastic

Cable

Number of wires 1,5 mm ² - 40% filling degree	44
Number of wires 2,5 mm ² - 40% filling degree	32

Equipment

Number of fix dividers	1
Compartment quantity	2

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------