



SL200552D4



Trunking lid SL20055 cherry

Technical properties

Dimensions

Trunking height	55 mm
Length	2000 mm
Trunking width	20 mm

Cover, door

Lid mounting	External
Lid with softlip	No
Lid width	20 mm

Materials

Material group	plastic
----------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------