



SL200552D4



Trunking lid SL20055 cherry

Technical properties

Dimensions

Trunking height	55 mm
Length	2000 mm
Trunking width	20 mm

Cover, door

Lid mounting	External
Lid with softlip	No
Lid width	20 mm

Materials

Material group	plastic
----------------	---------

Standards

Approvals	CE
European directive RoHS	voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------