



SL200552D5



## Trunking lid SL20055 aok

### Technical properties

#### Dimensions

Trunking height	55 mm
Length	2000 mm
Trunking width	20 mm

#### Cover, door

Lid mounting	External
Lid with softlip	No
Lid width	20 mm

#### Materials

Material group	plastic
----------------	---------

#### Standards

Approvals	CE
European directive RoHS	voluntary compliance

#### Safety

Halogen free	No
Impact strength	IK07

#### Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

#### temperatur

Ambient temperature	5...60 °C
---------------------	-----------