



SL2005539010



External corner VDI for trunking tehalit.SL 20x55mm pure white

Technical properties

Architecture

Fixing mode	Clamping
-------------	----------

Dimensions

Trunking height	55 mm
Trunking width	20 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

RAL colour	RAL 9010 - Pure white
Material group	plastic
Type of surface treatment	untreated

Settings

Angle range	83 / 135 °
-------------	------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------