



SL200553D4



External corner VDI for trunking tehalit.SL 20x55mm cherry

Technical properties

Dimensions

Trunking height	55 mm
Trunking width	20 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

Material group	plastic
----------------	---------

Settings

Angle range	83 / 135 °
-------------	------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

Approvals	CE
European directive RoHS	voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------