



SL200553D5



External corner VDI for trunking tehalit.SL 20x55mm oak

Technical properties

Architecture

Fixing mode Clamping

Dimensions

Trunking height 55 mm

Trunking width 20 mm

Cover, door

Lid with softlip No

Materials

Material group plastic

Settings

Angle range 83 / 135 °

Accessories included

Accessory configuration Moulded

Standards

Approvals CE

European directive RoHs voluntary compliance

temperatur

Ambient temperature -5...65 °C