



SL200554D2



Internal corner VDI for trunking tehalit.SL 20x55mm beech

Technical properties

Dimensions

| | |
|-----------------|-------|
| Trunking height | 55 mm |
| Trunking width | 20 mm |

Cover, door

| | |
|------------------|----|
| Lid with softlip | No |
|------------------|----|

Materials

| | |
|----------------|---------|
| Material group | plastic |
|----------------|---------|

Settings

| | |
|-------------|------------|
| Angle range | 83 / 135 ° |
|-------------|------------|

Accessories included

| | |
|-------------------------|---------|
| Accessory configuration | Moulded |
|-------------------------|---------|

Standards

| | |
|-------------------------|----------------------|
| Approvals | CE |
| European directive RoHS | voluntary compliance |

Safety

| | |
|-----------------|------|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| Impact strength | IK07 |

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | 5...60 °C |
|-----------------------|-----------|

temperatur

| | |
|---------------------|-----------|
| Ambient temperature | 5...60 °C |
|---------------------|-----------|