



SL200554D4



### Internal corner VDI for trunking tehalit.SL 20x55mm cherry

#### Technical properties

##### Architecture

Fixing mode Clamping

##### Dimensions

Trunking height 55 mm

Trunking width 20 mm

##### Cover, door

Lid with softlip No

##### Materials

Material group plastic

Type of surface treatment Tampography

##### Settings

Angle range 83 / 135 °

##### Accessories included

Accessory configuration Moulded

##### Standards

European directive RoHs voluntary compliance

##### Safety

Impact strength IK07

##### Use conditions

Operating temperature 5...60 °C

##### temperatur

Ambient temperature 5...60 °C