



SL20055911D1



## acc.box univ. SL20055 alu

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Device installation compatible format	Standard 60mm
---------------------------------------	---------------

#### Dimensions

Depth of installed product	48 mm
Height of installed product	145 mm
Trunking height	55 mm
Length	102 mm
Trunking width	20 mm
Format	overhanging wiring accessory

#### Materials

Colour	aluminium
Colour	aluminium optics
Material	plastic
Material group	mixed material
Type of surface treatment	Painted

#### Installation, mounting

Mounting way	horizontal
--------------	------------

#### Accessories included

Fitted with	empty
-------------	-------

#### Equipment

Number of units	1
-----------------	---

#### Standards

Approvals	CE
European directive RoHS	voluntary compliance

#### Safety

Protection index IP	IP40
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

**Use conditions**

Operating temperature	5...60 °C
-----------------------	-----------

**temperatur**

Ambient temperature	5...60 °C
---------------------	-----------