



SL20055AD2



acc.box coupling SL20055 beech

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Dimensions

Height of installed product 22 mm

Trunking height 55 mm

Length 110 mm

Trunking width 20 mm

Materials

Material group plastic

Installation, mounting

Mounting way horizontal

Standards

Approvals CE

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

Use conditions

Operating temperature 5...60 °C

temperatur

Ambient temperature 5...60 °C