



SL20055AD4



**acc.box coupling SL20055 cherry**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Configuration**

Antibacterial treatment No

**Dimensions**

Height of installed product 22 mm

Trunking height 55 mm

Length 110 mm

Trunking width 20 mm

**Materials**

Material group plastic

**Installation, mounting**

Mounting way horizontal

**Standards**

Approvals CE

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

**Use conditions**

Operating temperature 5...60 °C

**temperatur**

Ambient temperature 5...60 °C