



SL200802D1



Trunking lid SL20080 alu

Technical properties

Dimensions

| | |
|-----------------|---------|
| Trunking height | 80 mm |
| Length | 2000 mm |
| Trunking width | 20 mm |

Cover, door

| | |
|------------------|----------|
| Lid mounting | External |
| Lid with softlip | No |
| Lid width | 20 mm |

Materials

| | |
|----------------|---------|
| Material group | plastic |
|----------------|---------|

Standards

| | |
|-------------------------|----------------------|
| Approvals | CE |
| European directive RoHS | voluntary compliance |

Safety

| | |
|-----------------|------|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Impact strength | IK07 |

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | 5...60 °C |
|-----------------------|-----------|

temperatur

| | |
|---------------------|-----------|
| Ambient temperature | 5...60 °C |
|---------------------|-----------|