




SL200803D1



External corner VDI for trunking tehalit.SL 20x80mm alu

Technical properties

Architecture

Fixing mode Clamping

Dimensions

Trunking height 80 mm

Trunking width 20 mm

Cover, door

Lid with softlip No

Materials

Colour aluminium

Material group plastic

Type of surface treatment Painted

Settings

Angle range 83 / 135 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHs voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature 5...60 °C

temperatur

Ambient temperature 5...60 °C