




SL200803D6



External corner VDI for trunking tehalit.SL 20x80mm sucupira

Technical properties

Architecture

Fixing mode Clamping

Dimensions

Trunking height 80 mm

Trunking width 20 mm

Cover, door

Lid with softlip No

Materials

Material group plastic

Settings

Angle range 83 / 135 °

Accessories included

Accessory configuration Moulded

Standards

Approvals CE

European directive RoHs voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

Use conditions

Operating temperature 5...60 °C

temperatur

Ambient temperature 5...60 °C