



SL200804D3



**Internal corner VDI for trunking tehalit.SL 20x80mm mable**

**Technical properties**

**Dimensions**

|                 |       |
|-----------------|-------|
| Trunking height | 80 mm |
| Trunking width  | 20 mm |

**Cover, door**

|                  |    |
|------------------|----|
| Lid with softlip | No |
|------------------|----|

**Materials**

|                |         |
|----------------|---------|
| Material group | plastic |
|----------------|---------|

**Settings**

|             |            |
|-------------|------------|
| Angle range | 83 / 135 ° |
|-------------|------------|

**Accessories included**

|                         |         |
|-------------------------|---------|
| Accessory configuration | Moulded |
|-------------------------|---------|

**Standards**

|                         |                      |
|-------------------------|----------------------|
| Approvals               | CE                   |
| European directive RoHS | voluntary compliance |

**Safety**

|                 |      |
|-----------------|------|
| REACH conform   | Yes  |
| RoHS conform    | Yes  |
| Halogen free    | Yes  |
| Impact strength | IK07 |

**Use conditions**

|                       |           |
|-----------------------|-----------|
| Operating temperature | 5...60 °C |
|-----------------------|-----------|

**temperatur**

|                     |           |
|---------------------|-----------|
| Ambient temperature | 5...60 °C |
|---------------------|-----------|