



SL200807D1



Joint cover for trunking tehalit.SL 20x80mm alu

Technical properties

Architecture

Fixing mode	Clamping
-------------	----------

Dimensions

Trunking height	80 mm
Trunking width	20 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	aluminium
Material	PC-ABS
Material group	plastic
Type of surface treatment	Painted

Standards

Approvals	CE
European directive RoHS	voluntary compliance

Safety

Protection index IP	IP40
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------