



SL200807D2



## Joint cover for trunking tehalit.SL 20x80mm beech

### Technical properties

#### Architecture

Fixing mode	Clamping
-------------	----------

#### Dimensions

Trunking height	80 mm
Trunking width	20 mm

#### Cover, door

Lid with softlip	-
------------------	---

#### Materials

Material group	plastic
----------------	---------

#### Standards

Approvals	CE
European directive RoHs	voluntary compliance

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

#### Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

#### temperatur

Ambient temperature	5...60 °C
---------------------	-----------