



SL200809609010

acc.box SL20080 2 x gang (Fr) pw

Technical properties

Architecture

Connection system	Other
Fixing mode	Clamping and screwable

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Device installation compatible format	45x45 mm
---------------------------------------	----------

Main electrical features

Nominal voltage	230 V
-----------------	-------

Dimensions

Trunking height	80 mm
Trunking width	20 mm
Format	overhanging wiring accessory

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Material group	mixed material

Installation, mounting

Mounting way	horizontal
--------------	------------

Accessories included

Fitted with	socket outlet
-------------	---------------

Equipment

Number of units	2
-----------------	---

Standards

Approvals	CE
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Impact strength	IK07

Use conditions

Operating temperature

5...60 °C

temperatur

Ambient temperature

5...60 °C

Identification

Version

F