



SL20080960D1

acc.box SL20080 2 x gang (Fr) alu

Technical properties

Architecture

Connection system	Other
Fixing mode	Clamping and screwable

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Device installation compatible format	45x45 mm
---------------------------------------	----------

Main electrical features

Nominal voltage	230 V
-----------------	-------

Dimensions

Trunking height	80 mm
Trunking width	20 mm
Format	overhanging wiring accessory

Materials

Colour	aluminium
Colour	aluminium optics
Material	Mixed materials
Material group	mixed material
Type of surface treatment	Painted

Installation, mounting

Mounting way	horizontal
--------------	------------

Accessories included

Fitted with	socket outlet
-------------	---------------

Equipment

Number of units	2
-----------------	---

Standards

Approvals	CE
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Impact strength	IK07

Use conditions

Operating temperature

5...60 °C

temperatur

Ambient temperature

5...60 °C

Identification

Version

F