



SL20080AD1



**acc.box coupling SL20080 alu**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Dimensions**

Height of installed product	33 mm
Trunking height	80 mm
Length	110 mm
Trunking width	20 mm

**Materials**

Material group	plastic
----------------	---------

**Installation, mounting**

Mounting way	horizontal
--------------	------------

**Standards**

Approvals	CE
European directive RoHS	voluntary compliance

**Safety**

REACH conform	Yes
RoHS conform	Yes
Impact strength	IK07

**Use conditions**

Operating temperature	5...60 °C
-----------------------	-----------

**temperatur**

Ambient temperature	5...60 °C
---------------------	-----------