



SL20080AD2



acc.box coupling SL20080 beech

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Dimensions

Height of installed product 33 mm

Trunking height 80 mm

Length 110 mm

Trunking width 20 mm

Materials

Material group plastic

Type of surface treatment Tampography

Installation, mounting

Mounting way horizontal

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature 5...60 °C

temperatur

Ambient temperature 5...60 °C