



SL20080AD4



acc.box coupling SL20080 cherry

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Height of installed product	33 mm
Trunking height	80 mm
Length	110 mm
Trunking width	20 mm

Materials

Material group	plastic
----------------	---------

Installation, mounting

Mounting way	horizontal
--------------	------------

Standards

Approvals	CE
European directive RoHS	voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------