



SL20080AD4



acc.box coupling SL20080 cherry

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Height of installed product	33 mm
Trunking height	80 mm
Length	110 mm
Trunking width	20 mm

Materials

Colour	cherry
Colour	cherry optics
Material	ABS
Material group	plastic
Type of surface treatment	Tampography

Installation, mounting

Mounting way	horizontal
--------------	------------

Standards

Approvals	CE
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------